

Double Speed Sprockets



Dimensions are in inches unless otherwise indicated.

Sprockets supplied without keyway and setscrews unless specifically requested.

No. Teeth	Outside Diameter D_o	Pitch Diameter D_p	Catalog Number	Plain Bore d	Hub Diameter D_h	Length Thru Bore LTB	Weight Lbs.
10	2.480	2.427	C2030W-10T	.500	1.457	.984	.44
10	3.346	3.236	C2040W-10T	.630	2.047	1.575	1.76
10	4.213	4.045	C2050W-10T	.630	2.598	1.772	3.31
10	5.039	4.854	C2060W-10T	.748	3.189	1.969	5.52
10	6.772	6.472	C2080W-10T	.906	4.331	2.638	15.40

Some sizes are Made-To-Order, consult iwis for availability.

