

No. 160 2" Pitch — QD®




160 QD® 2" Pitch

Pitch	Inner width	Roller- Ø
inch	inch	inch
2"	1 1/4"	1.125"

QD® is a registered trademark of Emerson Power Transmission Manufacturing, L.P.

Sprockets supplied without keyway and setscrews unless specifically requested.



No. Teeth	Outside Diameter	Pitch Diameter	Catalog Number	Bushing	Max. Bore	Type	Hub Dia.	LTB	X	Y	L	Wt. Lbs.
12	8.660	7.728	160E12	E	3 1/2	B	6	1 5/8	2 15/16	2 5/8	1 5/16	11.00
13	9.310	8.358	160E13	E	3 1/2	B	6	1 5/8	2 15/16	2 5/8	1 5/16	14.00
14	9.960	8.988	160E14	E	3 1/2	B	6	1 5/8	2 15/16	2 5/8	1 5/16	16.00
15	10.610	9.620	160F15	F	3 15/16	B	6 5/8	2 1/2	4	3 5/8	2 5/16	24.00
16	11.260	10.252	160F16	F	3 15/16	B	6 5/8	2 1/2	4	3 5/8	2 5/16	27.00
17	11.900	10.844	160F17	F	3 15/16	B	6 5/8	2 1/2	4	3 5/8	2 5/16	31.00
18	12.540	11.518	160F18	F	3 15/16	B	6 5/8	2 1/2	4	3 5/8	2 5/16	35.00
19	13.190	12.152	160F19	F	3 15/16	B	6 5/8	2 1/2	4	3 5/8	2 5/16	38.00
20	13.830	12.784	160F20	F	3 15/16	B	6 5/8	2 1/2	4	3 5/8	2 5/16	42.00
21	14.740	13.420	160F21	F	3 15/16	B	6 5/8	2 1/2	4	3 5/8	2 5/16	45.00
22	15.110	14.054	160F22	F	3 15/16	B	6 5/8	2 1/2	4	3 5/8	2 5/16	51.00
23	15.750	14.688	160F23	F	3 15/16	B	6 5/8	2 1/2	4	3 5/8	2 5/16	55.00
24	16.390	15.322	160F24	F	3 15/16	B	6 5/8	2 1/2	4	3 5/8	2 5/16	59.00
25	17.030	15.958	160F25	F	3 15/16	B	6 5/8	2 1/2	4	3 5/8	2 5/16	64.00
26	17.670	16.592	160J26	J	4 7/16	C	7 1/4	3 3/16	5	4 1/2	1 3/16	74.00
28	18.950	17.862	160J28	J	4 7/16	C	7 1/4	3 3/16	5	4 1/2	1 3/16	84.00
30	20.230	19.134	160J30	J	4 7/16	C	7 1/4	3 3/16	5	4 1/2	1 3/16	96.00
35	23.420	22.312	160J35	J	4 7/16	C	7 1/4	3 3/16	5	4 1/2	1 3/16	116.00
40	26.610	25.492	160M40	M	5 1/2	C	9	5 3/16	6 3/4	6 3/4	2 11/16	174.00
45	29.800	28.672	160M45	M	5 1/2	C	9	5 3/16	6 3/4	6 3/4	2 11/16	208.00
54	35.540	34.396	160M54	M	5 1/2	C	9	5 3/16	6 3/4	6 3/4	2 11/16	262.00
60	39.360	38.214	160M60	M	5 1/2	C	9	5 3/16	6 3/4	6 3/4	2 11/16	310.00
70	45.730	44.578	160M70	M	5 1/2	C	9	5 3/16	6 3/4	6 3/4	2 11/16	431.00
80	52.100	50.942	160M80	M	5 1/2	C	9	5 3/16	6 3/4	6 3/4	2 11/16	530.00

QD® Bushings

Bushing	Bore Range		No Keyway	Wt. Lbs.
	Standard Keyway	Shallow Keyway		
E	7/8 — 2 3/4	2 13/16 — 3 7/16	3 1/2	10.00
F	1 — 3 1/4	3 5/16 — 3 15/16	4	11.50
J	1 7/16 — 3 3/4	3 13/16 — 4 1/2	—	18.00
M	2 — 4 3/4	4 7/8 — 5 1/2	—	37.00

Some sizes are Made-To-Order, consult iwiss for availability.