



iwis Customer Service

CallBack Tel: +49 2739 86-21 Fax: -22


E-Mail: sales-wilnsdorf@iwis.com

iwis
antriebssysteme
wir bewegen die welt

FLEXON® Scharnierbandkette Serie 879

Flat Top Chain Series 879

879



* 41,5 Kurve
Curve
44,5 Gerade
Straight

Werkstoff Kette Chain material	LF / KV ¹⁾
Werkstoff Bolzen Pin material	Edelstahl Stainless steel
Plattendicke Plate thickness	4,8 mm
Bolzendurchmesser Pin diameter	7,14 mm
Rückbiegeradius Back flex radius	50 mm
Min. Kurvenradius (R) Min. Curve radius	500 mm / 18"
Standardlänge Standard length	80 Pitches (10 feet - 3,048 m)



83-85
94-95



107



110



114



CAD

Kettentyp Chain ref	Werkstoff Material	Breite (L) Width		Durchschn. Bruchlast Average breaking load		Gewicht Weight	
		mm	inch	N	lbf	kg/m	lb/ft
LF879-K325	LF	82,5	3 1/4	6.000	1.325	0,98	0,66
LF879-K450		114,3	4 1/2			1,08	0,73
KV879-K325	KV	82,5	3 1/4	6.000	1.325	0,98	0,66
KV879-K450		114,3	4 1/2			1,08	0,73

SPEZIFIKATIONEN

- Scharnierbandketten der Serie 879 haben eine auf 4,8 mm verstärkte Platte und bieten somit eine um 20% höhere Verschleißlebensdauer als die Scharnierbandketten der Serie 880
- 4,8 mm Plattendicke ermöglicht den Transfer auf Scharnierbandketten der Serien 821 / 831 / 882 / 8257
- Durch den an der Unterseite angebrachten Schwalbenschwanz wird die Kette in der Kurve gehalten

CHARACTERISTICS

- Series 879 has thicker top plate of 4,8 mm offering 20% higher wear life than the original 880 series
- Series 879 offers matching transfer to 821 / 831 / 882 / 8257 series
- Bevel shoe on the underside of the chain to hold down in curve tracks

¹⁾ Hinweis:

Auf Anfrage erhältlich in:
Anti Static (AS), High Temperature (HT),
Grey Acetal Basic (D) und Chemical Resistant (PP)

Note:

Available upon request in:
Anti Static (AS), High Temperature (HT),
Grey Acetal Basic (D) and Chemical Resistant (PP)