


No. 120 1 1/2" Pitch — Multiple Strand



Pitch	Inner width	Roller- Ø
inch	inch	inch
1 1/2"	1"	.875"

† Dimensions shown allow for standard keyway with set screw at 90°

Sprockets supplied without keyway and setscrews unless specifically requested.



Basic Sprocket Dimensions				120-2 Double Strand				
No. Teeth	Outside Diameter	Pitch Diameter	Plain Bore	Catalog Number	Hub Dia.	LTB	†Max. Bore	Wt. Lbs.
11	6.010	5.325	1 1/2	D120B11	3 5/16	3 3/4	2 3/8	13.60
12	6.500	5.796	1 1/2	D120B12	4 1/16	3 3/4	2 3/4	17.30
13	6.990	6.269	1 1/2	D120B13	4 1/2	3 3/4	3	21.10
14	7.470	6.741	1 1/2	D120B14	5	3 3/4	3 5/16	25.60
15	7.960	7.215	1 1/2	D120B15	5 1/4	3 3/4	3 1/2	29.90
16	8.440	7.689	1 1/2	D120B16	5 3/4	3 3/4	3 1/2	33.80
17	8.920	8.163	1 1/2	D120B17	5 3/4	3 3/4	3 1/2	36.90
18	9.410	8.639	1 1/2	D120B18	5 3/4	3 3/4	3 1/2	41.90
19	9.890	9.114	1 1/2	D120B19	5 3/4	3 3/4	3 1/2	46.50
20	10.370	9.588	1 1/2	D120B20	5 1/2	3 3/4	3 1/2	50.20
21	10.850	10.065	1 1/2	D120B21	5 1/2	3 3/4	3 1/2	55.60
22	11.330	10.541	1 1/2	D120B22	5 3/4	4	3 13/16	64.00
23	11.810	11.016	1 1/2	D120B23	6 1/2	4	4 1/4	75.00
24	12.290	11.492	1 1/2	D120B24	6 1/2	4	4 1/4	79.00
25	12.780	11.969	1 1/2	D120B25	6 1/2	4	4 1/4	84.00
26	13.250	12.444	1 1/2	D120B26	6 1/2	4	4 1/4	90.00
30	15.170	14.351	1 1/2	D120B30	6 1/2	4	4 1/4	119.00

Some sizes are Made-To-Order, consult iwis for availability.