


No. 160 2" Pitch — Multiple Strand



Pitch	Inner width	Roller- Ø
inch	inch	inch
2"	1 1/4"	1.125"

† Dimensions shown allow for standard keyway with set screw at 90°

Sprockets supplied without keyway and setscrews unless specifically requested.



Basic Sprocket Dimensions				160-2 Double Strand				
No. Teeth	Outside Diameter	Pitch Diameter	Plain Bore	Catalog Number	Hub Dia.	LTB	†Max. Bore	Wt. Lbs.
13	9.310	8.358	2	D160B13	6	4 3/4	4	48.00
14	9.960	8.988	2	D160B14	6 3/4	4 3/4	4 3/4	58.00
15	10.610	9.620	2	D160B15	7	4 3/4	5 1/4	68.00
16	11.260	10.252	2	D160B16	7	4 3/4	5 1/4	75.00
17	11.900	10.844	2	D160B17	7	4 3/4	5 1/4	91.00
18	12.540	11.518	2	D160B18	7	4 3/4	5 1/4	96.00
19	13.190	12.152	2	D160B19	7	4 3/4	5 1/4	107.00
20	13.830	12.784	2	D160B20	7	4 3/4	5 1/4	119.00
21	14.470	13.420	2	D160B21	7 1/2	4 3/4	5 3/8	130.00
22	15.110	14.054	2	D160B22	7 1/2	4 3/4	5 3/8	141.00
23	15.750	14.688	2	D160B23	7 1/2	4 3/4	5 3/8	157.00
24	16.390	15.322	2	D160B24	7 1/2	4 3/4	5 3/8	171.00
25	17.030	15.958	2	D160B25	7 1/2	4 3/4	5 3/8	187.00
26	17.670	16.592	2	D160B26	7 1/2	4 3/4	5 3/8	201.00

Some sizes are Made-To-Order, consult iwis for availability.